

6267 National Gold Tube

6267 National Gold Tube

Voltages applied to the tube:	Filament Voltage	6.3V
	Plate Voltage	250.0V
	Screen Grid Voltage	140.0V
	Control Grid Voltage	-2.0V
Limits:	Max. Noise Level	8.0 mVrms
	Max. Microphonics	8.0 mVrms

A tube with a noise level greater than 8.0 mVrms would be rejected.

Microphonics are measured while the tube is being tapped. A tube with a microphonics measurement of 8.0 mVrms or less is accepted, while a tube with a measurement greater than 8.0 mVrms is rejected.

Output Current Scales For Matching

No.	No.
1. 2.10 mA - 2.28 mA	6. 3.01 mA - 3.18 mA
2. 2.29 mA - 2.46 mA	7. 3.19 mA - 3.36 mA
3. 2.47 mA - 2.64 mA	8. 3.37 mA - 3.54 mA
4. 2.65 mA - 2.82 mA	9. 3.55 mA - 3.72 mA
5. 2.83 mA - 3.00 mA	10. 3.73 mA - 3.90 mA