



PCC 189 Duotriode



Noval B9A



J_A - Bereich

A_I
●
90 V

A_{II}
●
90 V

●
30

J_A **15** mA

U_{II}

G_{III}

●

●

●

Meßspannungen

Heizung	F	7,2	V
U_I	G_{II}	1,2	-V
U_{II}	G_{III}	1,2	-V
U_{III}			V
U_{IV}			V
A		90	V

U_I
●
1,2 V
●
1,2 V

G_{II}

●

● K_I

K_{II} S

● F

● ●

● F

Richtströme

J_A	15	mA
J_{G_2}		mA
S	12,5	mA/V

Heizung 7,2 Volt

Meßkarte für NEUBERGER Röhrenmeßgeräte

